

TABLE OF CONTENTS



Chapter 1: Getting Started

Introduction	1-2
Conventions Used	1-3
DL05 Micro PLC Components	1-4
I/O Selection Quick Chart	1-5
Quick Start for PLC Checkout and Programming.....	1-6
Steps to Designing a Successful System	1-10
Questions and Answers about DL05 Micro PLCs.....	1-12

Chapter 2 - Installation, Wiring, and Specifications

Safety Guidelines	2-2
Orientation to DL05 Front Panel	2-5
Mounting Guidelines	2-7
Wiring Guidelines	2-11
System Wiring Strategies	2-14
Wiring Diagrams and Specifications	2-31
Glossary of Specification Terms	2-47

Chapter 3 - CPU Specifications and Operation

Introduction	3-2
CPU Specifications	3-3
CPU Hardware Setup	3-4
CPU Operation.....	3-11
I/O Response Time	3-15

CPU Scan Time Considerations	3-18
Memory Map	3-22
DL05 System V-memory	3-26
DL05 Aliases	3-29
X Input Bit Map	3-30
Y Output Bit Map	3-30
Control Relay Bit Map	3-31
Stage Control/Status Bit Map	3-32
Timer Status Bit Map	3-32
Counter Status Bit Map	3-33
 Chapter 4 - Configuration and Connections	
In this Chapter	4-1
DL05 System Design Strategies	4-2
Network Configuration and Connections	4-4
Network Slave Operation	4-8
Network Master Operation	4-14
 Chapter 5 - Standard RLL and Intelligent Box Instructions	
Introduction	5-2
Using Boolean Instructions	5-4
Boolean Instructions	5-9
Comparative Boolean	5-25
Immediate Instructions	5-31
Timer, Counter and Shift Register Instructions	5-35
Accumulator/Stack Load and Output Data Instructions	5-48
Logical Instructions (Accumulator)	5-60
Math Instructions	5-68
Bit Operation Instructions	5-82
Number Conversion Instructions (Accumulator)	5-87

Table Instructions 5-96

CPU Control Instructions..... 5-99

Program Control Instructions 5-101

Interrupt Instructions 5-108

Message Instructions..... 5-111

Intelligent I/O Instructions..... 5-118

Network Instructions 5-120

Intelligent Box (IBox) Instructions..... 5-124

Chapter 6 - Drum Instruction Programming

DL05 Drum Introduction 6-2

Step Transitions 6-4

Overview of Drum Operation 6-8

Drum Control Techniques 6-10

Drum Instruction 6-12

Event Drum (EDRUM) Instruction..... 6-14

Chapter 7 - RLL^{Plus} Stage Programming

Introduction to Stage Programming 7-2

Learning to Draw State Transition Diagrams..... 7-3

Using the Stage Jump Instruction for State Transitions 7-7

Stage Program Example: Toggle On/Off Lamp Controller..... 7-8

Four Steps to Writing a Stage Program 7-9

Stage Program Example: A Garage Door Opener..... 7-10

Stage Program Design Considerations..... 7-15

Parallel Processing Concepts..... 7-19

RLL^{Plus} Stage Instructions..... 7-21

Questions and Answers about Stage Programming 7-25

Chapter 8 - PID Loop Operation

DL05 PID Control.....	8-2
Introduction to PID Control.....	8-4
Introducing DL05 PID Control	8-6
PID Loop Operation.....	8-9
Ten Steps to Successful Process Control.....	8-16
PID Loop Setup.....	8-18
PID Loop Tuning.....	8-40
Using Other PID Features.....	8-53
Ramp/Soak Generator	8-58
DirectSOFT Ramp/Soak Example	8-63
Cascade Control.....	8-65
Time-Proportioning Control.....	8-68
Feedforward Control	8-70
PID Example Program	8-72
Troubleshooting Tips.....	8-75
Glossary of PID Loop Terminology	8-77
Bibliography	8-79

Chapter 9 - Maintenance and Troubleshooting

Hardware System Maintenance	9-2
Diagnostics.....	9-2
CPU Indicators	9-6
Communications Problems	9-7
I/O Point Troubleshooting	9-8
Noise Troubleshooting	9-10
Machine Startup and Program Troubleshooting	9-11

Chapter 10 - Memory Cartridge/Real Time Clock (DL05 Only)

General Information about the D0-01MC.....	10-2
Setting the Write Enable/Disable Jumper	10-3
Plugging-in the Memory Cartridge	10-4
Software and Firmware Requirements	10-5
Naming the Memory Cartridge	10-6
Setting the Time and Date.....	10-7
Memory Transfers.....	10-8
LED Indicator Lights	10-9
Password Protected Programs	10-9
Memory Map and Forwarding Range.....	10-10
Battery Back-up During AC Power Loss.....	10-11
Specifications and Agency Approvals	10-12
Clock/Calendar Instructions	10-13
Error Codes	10-18

Appendix A - Auxiliary Functions

Introduction.....	A-2
AUX 2* — RLL Operations.....	A-4
AUX 3* — V-memory Operations.....	A-4
AUX 4* — I/O Configuration.....	A-5
AUX 5* — CPU Configuration	A-5
AUX 6* — Handheld Programmer Configuration	A-8
AUX 7* — EEPROM Operations.....	A-8
AUX 8* — Password Operations	A-9

Appendix B - DL05 Error Codes

Appendix C - Instruction Execution Times

Introduction.....	C-2
Instruction Execution Times.....	C-3

Appendix D - Special Relays

DL05 PLC Special Relays.....	D-2
------------------------------	-----

Appendix E - High-Speed Input and Pulse Output Features

Introduction.....	E-2
Choosing the HSIO Operating Mode.....	E-4
Mode 10: High-Speed Counter.....	E-6
Mode 20: Quadrature Counter.....	E-18
Mode 30: Pulse Output.....	E-24
Trapezoidal Profile Operation.....	E-31
Registration Profile Operation.....	E-34
Velocity Profile Operation.....	E-42
Mode 40: High-Speed Interrupts.....	E-47
Mode 50: Pulse Catch Input.....	E-52
Mode 60: Discrete Inputs with Filter.....	E-55

Appendix F - PLC Memory

DL05 PLC Memory.....	F-2
----------------------	-----

Appendix G - ASCII Table

ASCII Table.....	G-2
------------------	-----

Appendix H - Product Weights

Product Weight Table.....	H-2
---------------------------	-----

Appendix I - Numbering Systems

Introduction.....	I-2
Binary Numbering System	I-2
Hexadecimal Numbering System.....	I-3
Octal Numbering System	I-4
Binary Coded Decimal (BCD) Numbering System	I-5
Real (Floating Point) Numbering System	I-5
BCD/Binary/Decimal/Hex/Octal - What is the Difference?.....	I-6
Data Type Mismatch.....	I-7
Signed vs. Unsigned Integers.....	I-8
AutomationDirect.com Products and Data Types	I-9

Appendix J - European Union Directives (CE)

European Union (EU) Directives	J-2
Basic EMC Installation Guidelines	J-5

Appendix K - Introduction to Serial Communications

Introduction to Serial Communications.....	K-2
--	-----